

# systemtronic

datasheet HOLD DAILY



General description:

The new version Hold Daily is each time nearer to the perfect auxiliar furniture for working spaces. Higher than the Hold Office, not only has more capacity but also more movement facility thanks to its special casters of 64 mm of diameter.  
Available in two versions: Hold Daily DR with door and locker or Hold Daily BX without door.  
Produced in a folded steel sheet, painted with poliester paint.

Designer: Estudio Enblanc.





**Technical description:**

Material: Steel.


**Dimensions:**

Hold daily DR: 485x362x920 mm 19.09x14.25x36.22"

Hold daily BX: 485x362x920 mm 19.09x14.25x36.22"

**HOLD DAILY DR****HOLD DAILY BX**

SI units: mm

**Finishes:**

For its use in humid zones, an additional primer process is required before the paint.  
For finishes and special dimensions please consult.

**Maintenance:****-Polyester Paint:**

For dry dirt (dust), use a damp cloth. For greasy/oily stains (fingerprints), wipe with a sponge with water and dishwashing liquid. Rinse with a damp cloth. Avoid using products containing solvents and/or pure ethyl alcohol.

**-Aluminium-metal-glass-melamine-plastic:**

We recommend using normal cleaning products for delicate surfaces. Alcohol, solvents and abrasive agents must be avoided.